

Mar, 31st, 2015

RE: LFPCN41222

To: Our Valued Customers.

From: Littelfuse Product Management Team

Subject: A-rated DO-214AA SIDACtor® Devices Optimization

Littelfuse would like to implement die optimization on DO -214AA package A-rated SIDACtor® to achieve lower capacitance, while continuing supports good margin to meet the min lpp spec across all the various waveform defined in the datasheet spec

Please refer to next pages for optimized parameter and to attachment for affected Part number list

There are slight changes on capacitance ,no change on reliability, also there is no change to fit, form, and function of the finished product and electrical parameter.

Form, Fit, Function Changes: None Part Number Changes: None Effective Date: July, 1st, 2015

Effective Date: July, 1st, 2015 Migration Period: July 1st 2015 to Sep 1st 2015

Replacement Products: N/A

Last Time Buy: N/A

If you have any other question or concerns, please contact Littelfuse® local sales representative, or Meng Wang, Assistant Product Manager for further assistance.

We highly value your business and look forward to assisting you whenever possible.

Best Regards,

Meng Wang

Assistant Product Manager Commodity TVS and SIDACtor Tel: +86 510 85277701 ext – 7955 Mwang3@littelfuse.com



800 E. Northwest Highway Des Plaines, IL 60016

Product/Process Change Notice (PCN)

| PCN#: LFPCN41222 Date: Mar 31st | 2015 | Contact Information | | | | |
|--|---------------------|--|--|--|--|--|
| Product Identification: | | Name: Meng Wang | | | | |
| DO-214AA SIDACtor® | | Title: Assistant Product Manager | | | | |
| A-rating Products | | Phone #: +86 510 85277701- 7955 | | | | |
| Implementation Date for Change: | | Fax#: +86 510 85277700 | | | | |
| July 1 st 2015 | | E-mail: Mwang3@littelfuse.com | | | | |
| Category of Change: | Descri | otion of Change: | | | | |
| ☐ Assembly Process | Littelfu | se would like to implement die optimization on DO214AA | | | | |
| □ Data Sheet | packag | ge A-rated SIDACtor® to achieve lower capacitance, | | | | |
| □ Technology | while co | ontinuing supports good margin to meet the min lpp spec | | | | |
| ☐ Discontinuance/Obsolescence | | all the various waveform defined in the datasheet spec , | | | | |
| ☐ Equipment | | · | | | | |
| ☐ Manufacturing Site | | no change to Fit, Form and function | | | | |
| Raw Material | I NIS P | CN is to seek customer approval to implement this optimization | | | | |
| Testing | | | | | | |
| Fabrication Process | | | | | | |
| Other: | | | | | | |
| Important Dates: | -1 | | | | | |
| Qualification Samples Available: Ma | | · | | | | |
| Final Qualification Data Available: Ma | ar 31 st | 2015 | | | | |
| ☐ Date of Final Product Shipment: N/A | | | | | | |
| | | | | | | |
| Method of Distinguishing Changed Pro | duct | | | | | |
| ☐ Product Mark, N/A | | | | | | |
| □ Date Code, 5Gxxx | | | | | | |
| ☐ Other, | | | | | | |
| Demonstrated or Anticipated Impact of | n Form, | Fit, Function or Reliability: | | | | |
| N/A | | | | | | |
| LF Qualification Plan/Results: | | | | | | |
| available, see attached next page | | | | | | |
| Customer Acknowledgement of Receipt: Littelfuse requests you acknowledge receipt of this PCN. In your acknowledgement, you can | | | | | | |
| grant approval or request additional information. Littelfuse will assume the change is acceptable if no acknowledgement is received within 30 days | | | | | | |
| of this notice. Lack of any additional response within | n 90 days | of PCN issuance further constitutes acceptance of the change. | | | | |
| | | | | | | |

Datasheet change Summary

| | Capacitance | | | ITSM | | | |
|--------------------|-------------|--------------|--------|--------|--------|-------|--|
| Chango | be | before after | | fter | before | after | |
| Change Part Number | pF min | pF max | pF min | pF max | A min | A min | |
| P0080SALRP | 25 | 35 | 20 | 40 | 20 | 25 | |
| P0220SALRP | 25 | 150 | 20 | 40 | 20 | 25 | |
| P0300SALRP | 15 | 140 | 20 | 40 | 20 | 25 | |
| P0640SALRP | 40 | 60 | 15 | 40 | 20 | 25 | |
| P0720SALRP | 35 | 60 | 15 | 40 | 20 | 25 | |
| P0900SALRP | 25 | 55 | 15 | 40 | 20 | 25 | |
| P1100SALRP | 30 | 50 | 15 | 40 | 20 | 25 | |
| P1300SALRP | 25 | 45 | 15 | 40 | 20 | 25 | |
| P2100SALRP | 20 | 35 | 15 | 40 | 20 | 25 | |
| P2500SALRP | 20 | 35 | 15 | 40 | 20 | 25 | |
| P1200SALRP | 30 | 45 | 15 | 40 | 20 | 25 | |
| P1500SALRP | 25 | 40 | 15 | 40 | 20 | 25 | |
| P1800SALRP | 25 | 35 | 15 | 40 | 20 | 25 | |
| P2000SALRP | 25 | 35 | 15 | 40 | 20 | 25 | |
| P2300SALRP | 25 | 35 | 15 | 40 | 20 | 25 | |
| P2600SALRP | 20 | 35 | 15 | 40 | 20 | 25 | |
| P3100SALRP | 15 | 50 | 15 | 40 | 20 | 25 | |
| P3500SALRP | 15 | 50 | 15 | 40 | 20 | 25 | |
| P0080SAMCLRP | 25 | 55 | 10 | 35 | 20 | 25 | |
| P0220SAMCLRP | 25 | 50 | 10 | 35 | 20 | 25 | |
| P0300SAMCLRP | 15 | 35 | 10 | 35 | 20 | 25 | |
| P566P0300SALRP | n/a | n/a | 20 | 40 | n/a | 25 | |
| P651P3100SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P658P0300SARP | n/a | n/a | 20 | 40 | n/a | 25 | |
| P659P0640SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P675P1100SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P688P1100SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P695P0300SARP | n/a | n/a | 20 | 40 | n/a | 25 | |
| P697P1300SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P707P3100SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P712P0640SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P716P3500SARP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P776P2000SALRP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P779P1800SALRP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P807P0080SAMCLRP | n/a | n/a | 10 | 35 | n/a | 25 | |
| P811P1200SALRP | n/a | n/a | 15 | 40 | n/a | 25 | |
| P817P0080SALRP | n/a | n/a | 20 | 40 | n/a | 25 | |
| P818P0220SALRP | n/a | n/a | 20 | 40 | n/a | 25 | |



Littelfuse electronic(Wuxi)Co., Ltd East #3, Zhenfa 6 Road, Shuofang Industrial Park, Jiangsu, China

Memorandum

To: Those who may concern

From: Gimmy Shi, Senior Product Engineer, Littelfuse.

Date: Feb 28th, 2015

Subject: Qualification test result for All DO-214AA A rated SIDACtor® optimization

This report is to summarize the qualification result of P0080SALRP; P3100SALRP; P3500SALRP.. This test result covers all SMB A rating series and their special devices.

1. Qualification sample

| Product Series | Part Number | Assy Lot | Remark | | | |
|----------------|-----------------------------------|----------|---------------------------------|--|--|--|
| SMB series | SMB series P0080SALRP CONTROL LOT | | DC/AC Blocking/TC/PCT/H3TRB/RSH | | | |
| | P0080SALRP | TEST LOT | DC/AC Blocking/TC/PCT/H3TRB/RSH | | | |
| SMB series | P3100SALRP | TEST LOT | DC/AC Blocking/TC/PCT/H3TRB/RSH | | | |
| | series P3500SALRP TEST LOT | | DC/AC Blocking/TC/PCT/H3TRB/RSH | | | |
| | P3500SALRP TEST LOT | | DC/AC Blocking/TC/PCT/H3TRB/RSH | | | |
| | P3500SALRP | TEST LOT | DC/AC Blocking/TC/PCT/H3TRB/RSH | | | |

2. Reliability test items and result summary

Reliability Part Number: P0080SALRP; P3100SALRP; P3500SALRP

| Test Categor | Description | Contents | Part number | Lot type | SS/Lot | Lot Quantity | Result | ETR |
|-----------------|---------------------------|-------------------------------------|-------------|-------------|-------------------------------------|-----------------|------------------------|------------------------|
| | | P0080SALRP | CONTROL LOT | | 1 lot | | | |
| | JESD22-A113 | P3500SALRP | CONTROL LOT | | 1 lot | | | |
| | Pre-condition | Sensitivity Level 1 | P0080SALRP | TEST LOT | 120 | 1 lot | Passed | |
| | | Selisitivity Level 1 | P3100SALRP | TEST LOT | | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | |] |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | Passed | |
| | DC - AC Blocking | 125C , DC/AC bias(peak) = 80% rated | P3500SALRP | CONTROL LOT | | 1 lot | | - |
| | (HTRB) | VDRM.1008hrsc | P0080SALRP | TEST LOT | 77 | 1 lot | | |
| | (ITIKD) | V DRM, TOUGHISC | P3100SALRP | TEST LOT | | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| Temp Cycle | -65C +150C,100 cycle time | P0080SALRP | TEST LOT | 40 | 1 lot | Passed | ETR#65444 ETR#66140 | |
| | | P3100SALRP | TEST LOT | | 1 lot | | | |
| 1 | | | P3500SALRP | TEST LOT | | 3 lot | | ETR#53429 |
| 1 | | 85C/85%RH,80% Vdrm, 1008hs | P0080SALRP | CONTROL LOT | | 1 lot | Passed | ETR#54332 ETR#55477 |
| 1 | Reliaiblity H3RTB | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| Reliaiblity | | | P0080SALRP | TEST LOT | 40 | 1 lot | | |
| 1 | | P3100SALRP | TEST LOT | | 1 lot | ' | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | . I |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| Autoclave | 121C, 100%RH,96hrs | P0080SALRP | TEST LOT | 40 | 1 lot | Passed | | |
| | | P3100SALRP | TEST LOT | | 1 lot | | | |
| | | P3500SALRP | TEST LOT | | 3 lot | | . I | |
| | | | P0080SALRP | CONTROL LOT | 1 lot 1 lot 30 1 lot 1 lot | | | |
| | | | P3500SALRP | CONTROL LOT | | | | |
| 1 | RSH | 260C x 30sec | P0080SALRP | TEST LOT | | 1 lot | Passed | |
| | | | P3100SALRP | TEST LOT | | | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |



Expertise Applied | Answers Delivered

| Test Category | Description | Contents | Part number | Lot type | SS/Lot | Lot Quantity | Result | ETR |
|---------------|------------------------|-----------------------------|-------------|-------------|--------|--------------|---------|-----------|
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| | ITSM | | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | |
| | | | P3100SALRP | TEST LOT | | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| | Surge out 2x10us | +/- 1 hit, 10% IPP per step | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | |
| | | | P3100SALRP | TEST LOT | | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| | Surge out 8x20us | +/- 1 hit, 10% IPP per step | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | |
| | - | • | P3100SALRP | TEST LOT | | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| | Surge out 10x700us | +/- 1 hit, 10% IPP per step | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | ETR#65444 |
| | " | ,, , | P3100SALRP | TEST LOT | | 1 lot | | ETR#66140 |
| Parametric | | | P3500SALRP | TEST LOT | | 3 lot | | ETR#53429 |
| Parametric | | | P0080SALRP | CONTROL LOT | | 1 lot | | ETR#54332 |
| | 0 | | P3500SALRP | CONTROL LOT | | 1 lot | | ETR#55477 |
| | Surge out 10x1000us | +/- 1 hit. 10% IPP per step | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | DIMOGRA |
| | 10X1000us | | P3100SALRP | TEST LOT | | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | | |
| | Capaciatone | Bias 2V. 1MHZ | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | |
| | | | P3100SALRP | TEST LOT | | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | l | |
| | IS measurement | Kevtek | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | |
| | | Neyter | P3100SALRP | TEST LOT | 10 | 1 lot | | |
| | | | P3500SALRP | TEST LOT | | 3 lot | | |
| | | | P0080SALRP | CONTROL LOT | | 1 lot | | |
| | | | P3500SALRP | CONTROL LOT | | 1 lot | l | |
| | VS measurement | Keytek | P0080SALRP | TEST LOT | 10 | 1 lot | Passed | |
| | | y ten | P3100SALRP | TEST LOT | 10 | 1 lot | r asseu | |
| | | | P3500SALRP | TEST LOT | | 3 lot | l | |

Notes: All of qualification test were passed qualified LF critical standard.

3. FAB Process & Material Differences/Changes:

3.1 Wafer and Process Changes
There are die optimization in the FAB.

4. Assembly, Process & Material Differences/Changes:

4.1 Assembly and Process Changes
There are no significant changes in the assembly and process method.

5. Packaging Method

There will be no changes in the packing method.

6. Marking Method

There will be no changes in the marking method.

7. Physical Differences/Changes

There is no change in mechanical specification or package outline dimension (POD).

8. Electrical Characteristic Summary:

There is slight capacitance change in electrical characteristics. Characterization data is available upon request.

Littelfuse Page 2 of 3



9. Changed Part Identification

There is no change in Part Identification.

10. Recommendations & Conclusions:

Based on the test results, it was determined that the redesign chips for DO-214AA A-rated SIDACTor were qualified and certified for mass productions, please refer to attachment for affected part list

Littelfuse Page 3 of 3